

REGO-LOK™ for Securing CGA Fittings on Liquid Cylinders

Application

The REGO-LOK™ is designed for installation on the Rego T9450 and T9460 Series liquid cylinder valves to deter and prevent the removal of the CGA fitting from the valve. The REGO-LOK™ retains standard CGA outlet connection fittings so unauthorized persons do not remove the fitting. By use of a special one-way bolt, the REGO-LOK™ is secured to the valve. The REGO-LOK™ installs in a few minutes with the use of screwdrivers. REGO-LOK™ installs without valve disassembly, brazing, welding, or drilling. The REGO-LOK™ deters and prevents fitting removal by gas customers, however allows the replacement of fittings by authorized gas supplier plant personnel.

Use REGO-LOK™ for compliance with CGA SB-26 for medical and industrial liquid cylinders.


Features

- Stainless Steel REGO-LOK™ with one-way bolt.
 - Retrofit all common liquid cylinder valves.
 - Can be supplied on new Rego liquid cylinder valves.
 - REGO-LOK™ indicates "WARNING: DO NOT REMOVE"
 - Worn CGA fittings can be simply replaced by authorized personnel. Requires new 9464RL-6 Bolt
 - Can fit over existing fittings for CGA 540, CGA 440, CGA 295, CGA 320, and CGA 326. Check fitting hex size.
- NOTE: Rego supplied fitting P/N CGA580RL is required for REGO-LOK™ use with CGA 580 connection.*
- Prevents loosening of CGA fittings on valves.

Rego-Lok™



Satisfies CGA SB-26 and FDA requirements for medical and industrial liquid cylinders.



Ordering Information

Part Number	Item Description	Typical Service Connection
9464RL-0	REGO-LOK™ for 3/8" hex fittings	CGA 295
9464RL-1	REGO-LOK™ for 1/2" fittings	CGA 440, CGA 320 & CGA 326
9464RL-2	REGO-LOK™ for 1" fittings	CGA 540
9464RL-3	REGO-LOK™ for 1 1/2" hex CGA 580RL fitting by Rego	CGA 580
CGA580RL	3/8" MNPTxCGA for use with 9464RL-3	CGA 580

REGO-LOK™ is a registered trademark of Rego Patent applied for.